

Garant GRIDLINE

Drawer for swing-door cabinets, Width 20G, 16×16G, Drawer front height: 150mm**Order data**

| | |
|--------------|---------------|
| Order number | 940640 150 |
| GTIN | 4062406068219 |
| Item class | 9GI |

Description**Version:**

Drawers for installation in GridLine cabinets. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with dividing material.

Suitable for:

Cabinets No. 940001 – 940103; No. 940111 – 940113, No. 940801 – 940843.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Unsuitable for installation in sliding door cabinets.

Technical description

| | |
|-------------------------------------|----------------------|
| Weight | 16 kg |
| Drawer/pull-out shelf load capacity | 75 kg |
| Usable depth in G | 16 |
| Usable height | 125 mm |
| Usable width in G | 16 |
| Application range | Cabinet with shelves |
| Usable depth | 400 mm |

| | |
|--|--|
| Usable width | 400 mm |
| with individual drawer release system | no |
| Material thickness | 0.9 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Drawer usable width × usable depth in G | 16×16G |
| Type of product | Drawer |

Accessories

| | |
|---|--------------|
| Ribbed rubber mat for drawers Dimension in G 16X16 | 951910 16X16 |
| Comfort Close drawer closure damping system Load capacity of the drawer 75 kg | 950180 75 |
| Non-slip mats set for drawers,5 pieces Dimension in G 16X16 | 951885 16X16 |