

Garant GRIDLINE

**Top-mounted cabinet with drawer, Plain sheet metal swing doors, 36×16G,  
Height: 750mm****Order data**

Order number	940111 750
GTIN	4062406068790
Item class	9GI

**Description****Version:**

Equipped cabinet in 40×20G, with drawers 36×16G.

Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Drawers with front height 125 mm.

**Supplied with:**

Cabinet with shelves and drawers.

**Colour:**

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Handle positioning	bottom
Depth	500 mm
Weight	52 kg
Height	750 mm
Drawer runner extension (partial/full extension)	100 %
Width	1000 mm
Electronic locking system can be retrofitted	yes
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Number of drawers	1
ComfortClose	no
Usable height	595 mm
Cabinet fronts	Plain sheet metal swing door
Number of shelves	1
Drawer/pull-out shelf load capacity	75 kg
Depth in G	20
Drawer usable depth	400 mm
Width in G	40
Drawer usable width in G	36
Drawer usable depth in G	16
Drawer usable width	900 mm
Drawer usable area in G	36×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×16G

Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

## Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 750/800 mm	940501 750/800
Mat for drawers Dimension in G 36X16	951830 36X16
Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 750/800 mm	940511 750/800
Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
Drawer for swing-door cabinets, Width 40G Drawer front height 100 mm	940642 100
Ribbed rubber mat for drawers Dimension in G 36X16	951910 36X16
Inclined shelf for cabinet / compartment width in G 40	940560 40
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Drawer for swing-door cabinets, Width 40G Drawer front height 200 mm	940642 200
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets, Width 40G Drawer front height 150 mm	940642 150
Drawer for swing-door cabinets, Width 40G Drawer front height 125 mm	940642 125
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Non-slip mats set for drawers, 5 pieces Dimension in G 36X16	951885 36X16
Drawer for swing-door cabinets, Width 40G Drawer front height 300 mm	940642 300

Drawer for swing-door cabinets,Width 40G Drawer front height 75 mm

940642 75

Storage shelf for cabinet / compartment width in G 40

940550 40