

Garant**Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 4,3mm****Order data**

Order number	122690 4,3
GTIN	4045197706577
Item class	11E

Description**Version:**

3 guide chamfers for particularly high accuracy and surface quality at tight hole tolerances.

Asymmetrical tip geometry for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

Advantage:

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI).**

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB**.

Form **HE**: order with **No. 122690 + 129100HE**.

Technical description

Shank tolerance	h6
Nominal Ø D_c	4.3 mm
Number of cutting edges Z	2
Flute length L_c	36 mm
Feed f in GJS ADI > 800 N/mm ²	0.16 mm/rev.
Tolerance nominal Ø	h7
Shank Ø D_s	6 mm
Overall length L	74 mm

Data sheet

Standard	DIN 6537 L
recommended maximum drilling depth L ₂	29.6 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	135 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	white
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
GG	suitable	110 m/min	K
GGG	suitable	90 m/min	K
GJS, ADI > 800N/mm ²	suitable	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/122690-4,3>