

Garant
Machine tap for synchronised spindles HSS-E-PM Form E, TiAlN, M: M2,5

Order data

Order number	135743 M2,5
GTIN	4045197505224
Item class	11H

Description
Version:

Sturdy version with right-hand helix and shank to DIN 1835-B. Special geometry for use on machines with **synchronised spindle drives**. The tap is controlled by the synchronising spindle of the machine.

Special **TiAlN coating** for optimum tool life. For use with **emulsion** (fat content minimum 8%).

Form E (lead chamfer: 1.5 - 2 turns) for the deepest possible thread depths.

Note:

For use on synchronised spindles, the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures very high process reliability.

Thread type: M

Tool material: HSS E PM

Standard: Manufacturer's standard

Tolerance class: ISO 2X 6HX

Thread pitch: 0.45 mm

Overall length L: 70 mm

Shank $\varnothing D_s$: 6 mm

Shank square \square : 4.9 mm

Tapping hole \varnothing : 2.05 mm

Technical description

Number of clamping slots	3
Tapping hole \varnothing	2.05 mm
Thread pitch	0.45 mm
Number of cutting edges Z	3
Thread \varnothing	2.5 mm

Standard	Manufacturer's standard
Shank $\varnothing D_s$	6 mm
Overall length L	70 mm
Shank square \square	4.9 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread depth	6.25 mm
Thread type	M
Thread size	M2.5
Coating	TiAlN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	E
Helix angle	40 °
Shank	DIN 1835 B to h6
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Shank tolerance	h6
Type of threading tool	Machine tap for synchronous machining
Colour ring	blue
Type of product	Tap

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	32 m/min	N
Steel < 750 N/mm ²	suitable	32 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P

INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
CuZn	suitable only under restricted conditions	30 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		