

 GRIDLINE

## GridLine modular case cabinet, Height mm / number of storage shelves: 2000/6



### Order data

Order number	944241 2000/6
GTIN	4062406073527
Item class	9GI

### Description

#### Version:

Cabinet for protection against unauthorised access and storage for modular case No. 693330. Storage shelves with guide rails and stop rail at the back. Mountings for shelves at 25-mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock.

#### Supplied with:

Cabinet with storage shelves.

#### Colour:

Body light grey RAL 7035, doors anthracite RAL 7016 **powder-coated**.

#### Note:

Supplied without modular case.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Shelf load capacity / maximum distributed shelf load (on metal): 100 kg

Height: 2000 mm

Width: 500 mm

Depth: 500 mm

Width in G: 20

Depth in G: 20

Usable height: 1845 mm

## Technical description

Depth in G	20
Width	500 mm
Weight	81 kg
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Usable height	1845 mm
Width in G	20
Cabinet fronts	Viewing window swing door
Number of shelves	6
Height	2000 mm
Depth	500 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

## Accessories

Additional storage shelf for modular case cabinet for cabinet width in G 20 mm	944249 20
Push handle for GridLine Type GP11	914226 GP11