

Garant GRIDLINE

**Computer workstation, Type: GB****Order data**

Order number	948201 GB
GTIN	4062406074197
Item class	9GS

**Description****NOTE: Colour selection possible****Version:**

Cupboard with separately lockable double swing doors with polycarbonate window, equipped with dividing wall (can be mounted on the left or right), **pull-out shelf load capacity 45 kg**, with cable strain relief and galvanised storage shelf for the tower compartment. Locking with a common key. All the electrical items are fitted so that they do not protrude and are easily accessible. Storage shelf made of bamboo.

**Colour:**

Body RAL 7035 light grey, doors, drawer and pull-out shelves RAL 7016 anthracite, **powder-coated.**

**Note:**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 1000 mm

Width: 1000 mm

Depth: 700 mm

Width in G: 40

Depth in G: 28

Support cabinet usable height: 645 mm

## Technical description

Weight	97 kg
Depth in G	28
Height	1020 mm
Depth	700 mm
Width in G	40
Width	1000 mm
Support cabinet usable width left	700 mm
Support cabinet usable height	645 mm
Support cabinet usable width right	223 mm
Power supply	Mains operated
Plug type, input	G
Nominal voltage	250 V
On/Off switch	yes
Material thickness	0.9 mm
Door opening angle	250 °
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

## Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------