

Garant
Machine tap for through holes and blind holes, uncoated, Type: 3.7/8-12

Order data

Order number	130050 3.7/8-12
GTIN	4062406052973
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS

Threads per inch: 12

Thread \varnothing : 98.425 mm

Overall length L: 180 mm

Shank $\varnothing D_s$: 56 mm

Shank square \square : 44 mm

Tapping hole \varnothing : 96.4 mm

Technical description

Thread pitch	2.11 mm
Threads per inch	12
Thread depth	147.64 mm
Shank square \square	44 mm
Shank $\varnothing D_s$	56 mm
Overall length L	180 mm
Thread \varnothing	98.425 mm
Tapping hole \varnothing	96.4 mm

Number of cutting edges Z	10
Tool material	HSS
Number of clamping slots	10
Thread type	UN
Thread size	3.7/8-12 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap