

Garant
Machine tap for synchronised spindles HSS-E-PM IC / Form C, TiAlN, G: G3/8

Order data

Order number	137816 G3/8
GTIN	4045197705808
Item class	11H

Description
Version:

Sturdy version with right-hand helix and shank to DIN 1835-B. Special geometry for **general-purpose use** on machines with **synchronised spindle drive**. The tap is controlled by the synchronising spindle of the machine. Special **TiAlN-S coating** for optimum tool life. For use with **emulsion** (fat content minimum 8%).

With **internal coolant supply** for maximum tool life.

Application:

For Whitworth parallel pipe threads DIN-ISO 228/1 (threads that do not form a seal within the connection).

Note:

For use on synchronised spindles, the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures very high process reliability.

Tool material: HSS E PM

Threads per inch: 19

Thread Ø: 16.66 mm

Overall length L: 100 mm

Shank Ø D_s: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 15.25 mm

Technical description

Thread Ø	16.66 mm
Thread pitch	1.337 mm
Number of clamping slots	4
Threads per inch	19

Tapping hole \varnothing	15.25 mm
Number of cutting edges Z	4
Tool material	HSS E PM
Shank $\varnothing D_s$	12 mm
Overall length L	100 mm
Shank square \square	9 mm
Thread depth	49.98 mm
Thread size	G3/8
Coating	TiAlN
Thread type	G
Flank angle	55 °
Standard	Manufacturer's standard
Taper lead form	C
Helix angle	40 °
Shank	DIN 1835 B with h6
Through-coolant	yes
Application for type of drilling	up to 3xD for blind holes
Cutting direction	right-hand
Shank tolerance	h6
Type of threading tool	Machine tap for synchronous machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	32 m/min	N
Aluminium (short chipping)	suitable	32 m/min	N

Steel < 500 N/mm ²	suitable	33 m/min	P
Steel < 750 N/mm ²	suitable	32 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	7 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
CuZn	suitable only under restricted conditions	30 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		