

Garant
Machine tap for synchronised spindles HSS-E-PM, TiAlN, MF: 12X1

Order data

Order number	132950 12X1
GTIN	4045197704979
Item class	11H

Description
Version:

Sturdy design with spiral point and shank to DIN 1835-B. Special geometry for use on machines with **synchronised spindle drives**. The tap is controlled by the synchronising spindle of the machine. Special **TiAlN-S coating** for optimum tool life. For use with **emulsion** (fat content minimum 8%).

Note:

For use on synchronised spindles, the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures maximum process reliability.

Thread type: MF

Tool material: HSS E PM

Standard: Manufacturer's standard

Tolerance class: ISO 2X 6HX

Thread pitch: 1 mm

Overall length L: 100 mm

Shank $\varnothing D_s$: 12 mm

Shank square \square : 9 mm

Tapping hole \varnothing : 11 mm

Technical description

Thread \varnothing	12 mm
Number of clamping slots	4
Thread pitch	1 mm
Tapping hole \varnothing	11 mm
Number of cutting edges Z	4

Shank $\varnothing D_s$	12 mm
Overall length L	100 mm
Shank square \square	9 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Standard	Manufacturer's standard
Thread depth	36 mm
Thread type	MF
Thread size	M12x1
Coating	TiAlN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	DIN 1835 B with h6
Through-coolant	no
Application for type of drilling	up to 3xD for through holes
Cutting direction	right-hand
Shank tolerance	h6
Type of threading tool	Machine tap for synchronous machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	40 m/min	N
Aluminium (short chipping)	suitable	40 m/min	N
Steel < 500 N/mm ²	suitable	37 m/min	P

Steel < 750 N/mm ²	suitable	35 m/min	P
Steel < 900 N/mm ²	suitable	22 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	7 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	10 m/min	M
CuZn	suitable only under restricted conditions	35 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		