

## Garant

**Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC m6 (Ø DC X = h7)  
(mm or inch): 2,0-X**



### Order data

Order number	122659 2,0-X
GTIN	4062406075569
Item class	11E

### Description

**IMPORTANT: item is configurable**

Ø range: 2 - 2.99 mm, Intervall: 0,010

**Version:**

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. High roundness and alignment accuracy of the deep hole, thanks to **4 guide chamfers**. Outstanding chip evacuation due to **4 internal cooling channels** from Ø 3.8 mm. Up to 3.7 mm Ø with 2 internal cooling channels. **Straight major cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

**Attention:**

Sizes **ending with X** = cutter Ø tolerance **h7**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122661**.

Form **HE**: order with **No. 122659 + 129100HE**. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by  $\pm 10\%$  (minimum 1 piece).

Standard: DIN 6537

Tolerance nominal Ø: m6

Number of cutting edges Z: 2

Tolerance nominal Ø: m6

Overall length L: 57 mm

Shank Ø  $D_s$ : 4 mm

Feed f in stainless steel > 900 N/mm<sup>2</sup>: 0.05 mm/rev.

## Technical description

Overall length L	57 mm
Number of cutting edges Z	2
Tolerance nominal $\varnothing$	m6
Flute length $L_c$	21 mm
Feed f in stainless steel > 900 N/mm <sup>2</sup>	0.05 mm/rev.
Shank $\varnothing D_s$	4 mm
Standard	DIN 6537
$\varnothing$ range	2 - 2.99 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6xD
Point angle	140°
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	blue
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	70 m/min	P

INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	80 m/min	M
GG(G)	suitable	95 m/min	K
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		