

Garant
Left-hand thread through hole and blind hole machine tap, uncoated, Type: 3-8

Order data

Order number	130051 3-8
GTIN	4062406053789
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS

Threads per inch: 8

Thread \varnothing : 76.2 mm

Overall length L: 160 mm

Shank \varnothing D_s: 50 mm

Shank square \square : 39 mm

Tapping hole \varnothing : 73.2 mm

Technical description

Thread \varnothing	76.2 mm
Number of cutting edges Z	8
Tool material	HSS
Thread pitch	3.175 mm
Threads per inch	8
Shank \varnothing D _s	50 mm
Tapping hole \varnothing	73.2 mm

Thread depth	114.3 mm
Number of clamping slots	8
Overall length L	160 mm
Shank square □	39 mm
Thread type	UN-LH
Thread size	3-8 UN LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap