



**Solid carbide high performance drill, Weldon shank DIN 6535 HB, TiN, Ø DC  
h7: 12,06-Xmm**



## Order data

Order number	122315 12,06-X
GTIN	4062406076108
Item class	12E

## Description

### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ . Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by  $\pm 10\%$  (minimum 1 piece).

## Technical description

Flute length $L_c$	60 mm
Shank $\varnothing D_s$	14 mm
Standard	DIN 6537 K
Tolerance nominal $\varnothing$	h7
Feed $f$ in steel $< 900 \text{ N/mm}^2$	0.26 mm/rev.
Number of cutting edges $Z$	2
Overall length $L$	107 mm
$\varnothing$ range	12.06 - 14.05 mm

Coating	TiN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	no
Semi-Standard	yes
Colour ring	without
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	P
GG(G)	suitable only under restricted conditions	70 m/min	K
wet maximum	suitable		
dry	suitable		