

Garant

GARANT Master Steel SPEED solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7: 16,06-Xmm



Order data

| | |
|--------------|----------------|
| Order number | 122425 16,06-X |
| GTIN | 4062406077228 |
| Item class | 11E |

Description

Version:

Developed for use with **very high cutting speeds**. Outstandingly suitable for machines with **low power output** and high speeds.

- **Clear reduction in cutting forces due to special cutter geometry.**
- **Coating for best wear resistance even at high process temperatures.**
- **Polished flutes for good chip clearance.**

A **slim chisel edge** and the **special arrangement of the 4 guide chamfers** ensure **high positioning and alignment accuracy**. Optimised micro-geometry for increased working life and performance capability.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Versions HB and HE supplied at the same price as HA.

Form **HB**: state **No.122426** on the order.

Form **HE**: order with **No.122425 + 129100HE**. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

| | |
|---------------------|------------|
| Standard | DIN 6537 K |
| Tolerance nominal Ø | h7 |
| Flute length L_c | 73 mm |

| | |
|------------------------------------------|-------------------|
| Shank $\varnothing D_s$ | 18 mm |
| Overall length L | 123 mm |
| Feed f in steel < 1100 N/mm ² | 0.34 mm/rev. |
| Number of cutting edges Z | 2 |
| \varnothing range | 16.06 - 18.05 mm |
| Series | Master Steel |
| Coating | TiAlN |
| Tool material | solid carbide |
| Version | 4xD |
| Point angle | 135 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|-------------------------------------------|----------------|----------|
| Steel < 500 N/mm ² | suitable | 220 m/min | P |
| Steel < 750 N/mm ² | suitable | 200 m/min | P |
| Steel < 900 N/mm ² | suitable | 180 m/min | P |
| Steel < 1100 N/mm ² | suitable | 170 m/min | P |
| Steel < 1400 N/mm ² | suitable | 90 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 75 m/min | M |
| GG | suitable | 160 m/min | K |
| GGG | suitable | 130 m/min | K |
| Uni | suitable | | |

| | |
|-------------|----------|
| wet maximum | suitable |
| wet minimum | suitable |