

**Garant**
**Solid carbide HPC drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 3,76-Xmm**

**Order data**

Order number	122385 3,76-X
GTIN	4062406076825
Item class	11E

**Description**
**Version:**

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ . Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by  $\pm 10\%$  (minimum 1 piece).

**Technical description**

Flute length $L_c$	24 mm
Shank $\varnothing D_s$	6 mm
Standard	DIN 6537 K
Tolerance nominal $\varnothing$	h7
Feed $f$ in stainless steel $< 900 \text{ N/mm}^2$	0.09 mm/rev.
Overall length $L$	66 mm
Number of cutting edges $Z$	2
$\varnothing$ range	3.76 - 4.75 mm
Coating	TiAlN

Tool material	Solid carbide
Version	4×D
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	blue
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	245 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	85 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	55 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	50 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	35 m/min	S
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		