

Garant
Left-hand thread through hole and blind hole machine tap, TiN, Type: 2.3/4-18

Order data

Order number	130056 2.3/4-18
GTIN	4062406055875
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UNS-LH
 Tool material: HSS
 Threads per inch: 18
 Thread \varnothing : 69.85 mm
 Overall length L: 160 mm
 Shank \varnothing D_s: 50 mm
 Shank square \square : 39 mm
 Tapping hole \varnothing : 68.5 mm

Technical description

Thread pitch	1.411 mm
Tapping hole \varnothing	68.5 mm
Tool material	HSS
Number of clamping slots	8
Shank square \square	39 mm
Threads per inch	18
Thread \varnothing	69.85 mm

Shank $\varnothing D_s$	50 mm
Number of cutting edges Z	8
Thread depth	104.78 mm
Overall length L	160 mm
Thread type	UNS-LH
Thread size	2.3/4-18 UNS LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap