

Garant**Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 10,06-Xmm**

Order data

| | |
|--------------|----------------|
| Order number | 122500 10,06-X |
| GTIN | 4062406077662 |
| Item class | 11E |

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

NEW GENERATION AVAILABLE!

Recommended successor products are No. 122415; 122425; 122435 and 122361, as well as 122371.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122445/122505**.

Form **HE**: order with **No. 122440/122500** and **129100HE**. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

| | |
|--|--------------|
| Tolerance nominal Ø | h7 |
| Number of cutting edges Z | 2 |
| Standard | DIN 6537 K |
| Feed f in steel < 1100 N/mm ² | 0.27 mm/rev. |
| Shank Ø D _s | 12 mm |

| | |
|-----------------------------|-------------------|
| Overall length L | 102 mm |
| Flute length L _c | 55 mm |
| Ø range | 10.06 - 12.05 mm |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 4xD |
| Point angle | 140 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm ² | suitable only under restricted conditions | 120 m/min | P |
| Steel < 750 N/mm ² | suitable | 100 m/min | P |
| Steel < 900 N/mm ² | suitable | 85 m/min | P |
| Steel < 1100 N/mm ² | suitable | 65 m/min | P |
| Steel < 1400 N/mm ² | suitable | 35 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 30 m/min | M |
| Ti > 850 N/mm ² | suitable only under restricted conditions | 35 m/min | S |
| GG(G) | suitable | 70 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable | | |

Air

suitable