

Garant
Machine tap for through holes and blind holes, TiN, Type: 5-10

Order data

Order number	130055 5-10
GTIN	4062406055547
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS

Threads per inch: 10

Thread \varnothing : 127 mm

Overall length L: 180 mm

Shank \varnothing D_s: 56 mm

Shank square \square : 44 mm

Tapping hole \varnothing : 124.7 mm

Technical description

Shank square \square	44 mm
Threads per inch	10
Thread depth	190.5 mm
Shank \varnothing D _s	56 mm
Tapping hole \varnothing	124.7 mm
Number of clamping slots	12
Overall length L	180 mm
Tool material	HSS

Number of cutting edges Z	12
Thread pitch	2.54 mm
Thread Ø	127 mm
Thread type	UNS
Thread size	5-10 UNS
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap