

Garant
Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC m6 (mm or inch): 6,06-X

Order data

| | |
|--------------|---------------|
| Order number | 123008 6,06-X |
| GTIN | 4062406079796 |
| Item class | 11E |

Description
IMPORTANT: item is configurable

Ø range: 6.06 - 8.05 mm, Intervall: 0,010

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. High roundness and alignment accuracy of the deep hole, thanks to **4 guide chamfers**. Outstanding chip evacuation due to **4 internal cooling channels** from Ø 3.8 mm. Up to 3.7 mm Ø with 2 internal cooling channels. **Straight major cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

Note:

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 123010**.

Form **HE**: order with **No. 123008 + 129100HE**.

Flute length $L_c = L_2 + 1.5 \times D_c$. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Standard: Manufacturer's standard

Tolerance nominal Ø: m6

Number of cutting edges Z: 2

Tolerance nominal Ø: m6

Overall length L: 114 mm

Shank Ø D_s : 8 mm

Feed f in stainless steel $> 900 \text{ N/mm}^2$: 0.12 mm/rev.

Technical description

| | |
|---|-------------------------|
| Overall length L | 114 mm |
| Standard | Manufacturer's standard |
| Number of cutting edges Z | 2 |
| Shank $\varnothing D_s$ | 8 mm |
| Flute length L_c | 76 mm |
| Feed f in stainless steel > 900 N/mm ² | 0.12 mm/rev. |
| Tolerance nominal \varnothing | m6 |
| \varnothing range | 6.06 - 8.05 mm |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 8xD |
| Point angle | 140° |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | blue |
| Type of product | Jobber drill |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|-------------|----------|----------|
| Steel < 500 N/mm ² | suitable | 90 m/min | P |
| Steel < 750 N/mm ² | suitable | 75 m/min | P |
| Steel < 900 N/mm ² | suitable | 70 m/min | P |
| Steel < 1100 N/mm ² | suitable | 55 m/min | P |
| Steel < 1400 N/mm ² | suitable | 32 m/min | P |
| INOX < 900 N/mm ² | suitable | 70 m/min | M |
| INOX > 900 N/mm ² | suitable | 60 m/min | M |

| | |
|-------------|----------|
| wet maximum | suitable |
| wet minimum | suitable |