

Garant

Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 3,76-Xmm



Order data

Order number	122760 3,76-X
GTIN	4062406079567
Item class	11E

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Convex cutting edges with honed edges and special flute profile for **short chips**, even on long chipping materials.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122765**.

Form **HE**: order with **No. 122760 + 129100HE**.

NEW GENERATION AVAILABLE!

Recommended successor products are No. 122715; 122725 and 122651. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

Standard	DIN 6537
Number of cutting edges Z	2
Tolerance nominal Ø	h7
Shank Ø D _s	6 mm

Flute length L_c	36 mm
Overall length L	74 mm
Feed f in steel $< 1100 \text{ N/mm}^2$	0.11 mm/rev.
\varnothing range	3.76 - 4.75 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel $< 500 \text{ N/mm}^2$	suitable only under restricted conditions	120 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	100 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	85 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	65 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable	35 m/min	P
Steel $< 55 \text{ HRC}$	suitable	28 m/min	H
INOX $< 900 \text{ N/mm}^2$	suitable only under restricted conditions	30 m/min	M
Ti $> 850 \text{ N/mm}^2$	suitable only under restricted conditions	35 m/min	S
GG(G)	suitable	70 m/min	K
Uni	suitable		

wet maximum	suitable
Air	suitable