

Garant
Solid carbide milling cutter with chip separators TPC, TiAlN, Ø f8 DC: 14 mm

Order data

Order number	203083 14
GTIN	4045197706461
Item class	11X

Description
Version:

High-performance miller for machining superalloys, **especially designed for TPC applications.**
Strengthened core.

Note:

$h_{m \max}$: The values stated in the table are maximum values.

$a_{e \max} = 0.06 \times D$ for TPC machining.

Tolerance nominal Ø: f8

No. of teeth Z: 5

Helix angle: 45 degrees

Direction of infeed: horizontal and oblique

Shank: DIN 6535 HB to h6

Balance quality with shank: G 2.5 with HB

No. of teeth Z: 5

Flute length L_c : 42 mm

Overhang length L_1 incl. recess: 50 mm

Recess Ø D_1 : 13.8 mm

Overall length L: 99 mm

Shank Ø D_s : 14 mm

Technical description

Cutting edge Ø D_c	14 mm
Recess Ø D_1	13.8 mm
Average chip thickness h_{\max} for TPC milling in titanium > 850 N/mm ²	0.075 mm

No. of teeth Z	5
Overhang length L ₁ incl. recess	50 mm
Average chip thickness h _{max} for TPC milling in Inconel®	0.065 mm
Shank Ø D _s	14 mm
Overall length L	99 mm
Flute length L _c	42 mm
Direction of infeed	horizontal and oblique
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	f8
Balance quality with shank	G 2.5 with HB
Helix angle	45 degrees
Corner rounding r _v	0.3 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a _e for milling operation	0.06×D
Through-coolant	no
Machining strategy	TPC
Colour ring	pink
Type of product	End mill