

Garant
AN.U 120604, Type: GG


Order data

| | |
|--------------|---------------|
| Order number | 215111 GG |
| GTIN | 4045197703118 |
| Item class | 21A |

Description

Version:

Very sturdy double-sided 4-edge indexable insert.

The unique indexable insert geometry means the insert is not weakened by the securing hole.

Cutting data:

$a_{p\max} = 12$ mm.

$a_p = 10$ mm (recommendation).

Attention:

Not suitable for full-slot milling.

Note:

Side milling: Standard application values for $a_e = 0.3 \times D$ / $a_p = 10$ mm.

Corner radius: 0.4 mm

Feed f_z per tooth: 0.15 mm

Grade: HB9720

Technical description

| | |
|----------------------|---------|
| Feed f_z per tooth | 0.15 mm |
| Type | GG |

| | |
|---------------------------|------------------------------|
| Corner radius | 0.4 mm |
| Grade | HB9720 |
| Tolerance | K |
| ISO code indexable insert | AN.U 120604 |
| Tool material | Carbide |
| Type of product | Indexable insert for milling |