

Garant
Left-hand thread through hole and blind hole machine tap, uncoated, Type: 4.3/8-12

Order data

Order number	130051 4.3/8-12
GTIN	4062406054250
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS

Threads per inch: 12

Thread \varnothing : 111.1 mm

Overall length L: 180 mm

Shank \varnothing D_s: 56 mm

Shank square \square : 44 mm

Tapping hole \varnothing : 109.1 mm

Technical description

Thread \varnothing	111.1 mm
Number of cutting edges Z	12
Shank \varnothing D _s	56 mm
Overall length L	180 mm
Thread depth	166.7 mm
Tapping hole \varnothing	109.1 mm
Shank square \square	44 mm

Number of clamping slots	12
Tool material	HSS
Thread pitch	2.11 mm
Threads per inch	12
Thread type	UN-LH
Thread size	4.3/8-12 UN LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap