


**Garant****Arbor for screw-in milling cutters with thread cylindrical form, HSK-A 63,  
Thread M × Length L1: M16X25****Order data**

Order number	307042 M16X25
GTIN	4045197707000
Item class	31A

**Description****Version:**

Plain design.

With Balluff/RFID chip bore.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

**Note:**

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

**Technical description**

L <sub>2</sub>	5 mm
Reach L <sub>1</sub>	25 mm
Ø D <sub>2</sub>	29 mm
Overhang dimension A	51 mm
Thread M	M16×25
Bore Ø D <sub>1</sub>	17 mm

Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Threaded copy mill arbor