



## Ultradźwiękowe urządzenie do czyszczenia Elmasonic xtra ST, Typ: 60



### Dane zamówienia

Numer katalogowy	082002 60
GTIN	
Klasa artykułu	04S

### Opis

#### Wykonanie:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Elmasonic xtra ST is the ultrasonic device for the most severe dirt and is particularly suitable for extremely demanding applications in the field of industrial cleaning.

- **2 selectable ultrasonic frequencies (25 kHz for the most stubborn dirt and 45 kHz for gentle cleaning).**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Selectable pulse function increases the ultrasonic peak power.**
- **Dynamic function (ultrasonic power can be increased temporarily by up to 20%).**
- **Sturdy tray made from welded stainless steel.**

pojemność: 56,3 l

długość urządzenia: 825 mm

szerokość urządzenia: 595 mm

długość kosza wsadowego: 415 mm

Szerokość kosza wsadowego: 255 mm

wysokość pojemnika do czyszczenia: 330 mm

## Opis techniczny

wysokość pojemnika do czyszczenia	330 mm
długość urządzenia	825 mm
napięcie znamionowe	400 V
szerokość urządzenia	595 mm
zasilanie energią	Zasilanie sieciowe
długość kosza wsadowego	415 mm
Szerokość kosza wsadowego	255 mm
oznaczenie producenta	xtra ST 600H
moc grzewcza	1400 W
masa	55 kg
Moc szczytowa ultradźwięków	3600 W
pojemność	56,3 l
zalecana objętość robocza	45 l