



## Dados do pedido

Número do pedido	919923 250
GTIN	4017976247014
Classe de artigo	96D

## Descrição

### Modelo:

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

### Norma:

**EN 1757-3**

## Descrição técnica

Altura	780 mm
Ø da roda	200 mm
Altura da borda de descarga com rodas	780 mm
Medida altura da caixa	413 mm
Dimensões interiores de entrada, altura	72 mm

Largura	713 mm
Dimensões interiores de entrada, largura	194 mm
Medida comprimento da caixa	1200 mm
Volume do compartimento	250 l
Capacidade de carga	750 kg
Medida largura da caixa	652 mm
Comprimento	1359 mm
Peso	70 kg
Distância entre as aberturas de acesso B	203 mm
Tipo de produto	Contentor basculante