



## Dados do pedido

|                  |               |
|------------------|---------------|
| Número do pedido | 919923 600    |
| GTIN             | 4017976247038 |
| Classe de artigo | 96D           |

## Descrição

### Modelo:

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

### Norma:

**EN 1757-3**

## Descrição técnica

|   |         |
|---|---------|
| Peso                                    | 95 kg   |
| Capacidade de carga                     | 750 kg  |
| Ø da roda                               | 200 mm  |
| Dimensões interiores de entrada, altura | 72 mm   |
| Altura                                  | 1099 mm |

|  |                      |
|--|----------------------|
| Medida comprimento da caixa              | 1321 mm              |
| Volume do compartimento                  | 600 l                |
| Medida altura da caixa                   | 735 mm               |
| Comprimento                              | 1458 mm              |
| Dimensões interiores de entrada, largura | 194 mm               |
| Altura da borda de descarga com rodas    | 843 mm               |
| Distância entre as aberturas de acesso B | 327 mm               |
| Medida largura da caixa                  | 794 mm               |
| Largura                                  | 855 mm               |
| Tipo de produto                          | Contentor basculante |