



ÚDAJE O OBJEDNÁVKE

Číslo objednávky	078162 PFM17
GTIN	4061792210349
Trieda položky	03D

Popis

Prevedenie:

- **Fast, clean removal of welding beads in a single operation with the newly developed metal face mill.**
- **Face milling produces small metal chips (no metal dust which is hazardous to health).**
- **One-touch controller: patented, tool-free milling depth adjustment in 0.1 mm increments.**
- **Ready to use in seconds thanks to tool-free fixed magnetic guide rail (50 cm long, expandable).**
- **Simple, convenient changing of the inserts on the milling head.**
- **Slim handle area and large, tool-free adjustable bridge handle for safe, even guidance.**
- **Vario-Tacho-Constamatic (VTC) full-wave electronics with adjustment wheel: for working with material-appropriate speeds that remain constant under load.**
- **Electronic soft start and restart protection.**
- **With metaBOX, the intelligent solution for transport and storage.**

Technický opis

Odstupňovanie nastavenia hĺbky frézovania	0,1 mm
Blokovanie opätovného nábehu	áno
Výstupný výkon	970 W
maximálne vibrácie podľa EN	4,1 m/s ²
Hladina akustického výkonu (LwA)	102 dB(A)

Menovitý výkon	1700 W
Počet otáčok na voľnobeh	8000 - 12600 min ⁻¹
Úroveň hlasitosti	91 dB(A)
Balenie	Metabox
Spínač zapnutia/vypnutia	áno
Menovité napätie	230 V
Zásobovanie energiou	Sietová prevádzka
Hmotnosť	4,6 kg
Dĺžka kábla	3,6 m
Pozvoľný štart	áno
Druh produktu	Fréza