

metabo

ÚDAJE O OBJEDNÁVKE

Číslo objednávky	078126 KFM1615F
GTIN	
Trieda položky	03D

Popis

Prevedenie:

Metal edge milling cutter for chamfer heights up to 10 mm for weld seam preparation. One-touch controller. Patented, tool-free milling depth adjustment in 0.1 mm increments. Locking points for short setting times, to prevent unwanted adjustment of the milling depth when working. Precise adjustment of the bevel angle directly via the guide plates. Universal milling head with three carbide inserts for all bevel angles from 0 – 90°. Controlled working by means of large-area guide plates. Stop roller for guiding pipes for easy weld seam preparation. Loop handle which can be adjustable without using tools for safe and even guidance. Metabo Marathon motor with patented dust protection to ensure a long service life. Vario-Constamatic (VC) full-wave electronics with adjustment wheel, for working with material-appropriate speeds that remain virtually constant under load. Electronic overload protection, soft start and restart protection. User is protected by means of side plates to divert the chips. With metaBOX, the intelligent solution for transport and storage, illustration representative.

Technický opis

max výška skosenia 45°	15
Hmotnosť	6,9 kg
Hladina akustického výkonu (LwA)	104 dB(A)
Výstupný výkon	900 W
Počet otáčok na voľnobeh	12000 min ⁻¹

maximálne vibrácie podľa EN	2,5 m/s ²
Dĺžka kábla	4 m
max šírka skosenia 45°	21
Odstupňovanie nastavenia hĺbky frézovania	0,1 mm
Zaoblenia najmenšieho vonkajšieho Ø	100 mm
Menovitý výkon	1550 W
Úroveň hlasitosti	93 dB(A)
Uhol úkosu	0 - 90 Stupeň
Blokovanie opätovného nábehu	áno
Pozvoľný štart	áno
Druh produktu	Fréza