

**Garant**
**Machine tap for through holes and blind holes, TiN, Type: 3.3/4-4**

**Order data**

Order number	130055 3.3/4-4
GTIN	4062406055219
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNC

Tool material: HSS

Threads per inch: 4

Thread  $\varnothing$ : 95.25 mm

Overall length L: 180 mm

Shank  $\varnothing$  D<sub>s</sub>: 56 mm

Shank square  $\square$ : 44 mm

Tapping hole  $\varnothing$ : 88.76 mm

**Technical description**

Overall length L	180 mm
Tapping hole $\varnothing$	88.76 mm
Thread $\varnothing$	95.25 mm
Shank square $\square$	44 mm
Number of clamping slots	10
Thread pitch	6.35 mm
Threads per inch	4
Tool material	HSS

Shank $\varnothing D_s$	56 mm
Number of cutting edges Z	10
Thread depth	142.88 mm
Thread type	UNC
Thread size	3.3/4-4 UNC
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5xD for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap