

**Garant**
**Left-hand thread through hole and blind hole machine tap, TiN, Type: 3.3/4-16**

**Order data**

Order number	130056 3.3/4-16
GTIN	4062406056292
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS

Threads per inch: 16

Thread  $\varnothing$ : 95.25 mm

Overall length L: 180 mm

Shank  $\varnothing$  D<sub>s</sub>: 56 mm

Shank square □: 44 mm

Tapping hole  $\varnothing$ : 93.75 mm

**Technical description**

Number of clamping slots	10
Shank $\varnothing$ D <sub>s</sub>	56 mm
Overall length L	180 mm
Thread depth	142.88 mm
Tool material	HSS
Number of cutting edges Z	10
Threads per inch	16

Shank square □	44 mm
Thread pitch	1.588 mm
Thread Ø	95.25 mm
Tapping hole Ø	93.75 mm
Thread type	UN-LH
Thread size	3.3/4-16 UN LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap