

**Garant**
**Left-hand thread through hole and blind hole machine tap, uncoated, Type: 4-4**

**Order data**

Order number	130051 4-4
GTIN	4062406054175
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNC-LH

Tool material: HSS

Threads per inch: 4

Thread  $\varnothing$ : 101.6 mm

Overall length L: 180 mm

Shank  $\varnothing D_s$ : 56 mm

Shank square  $\square$ : 44 mm

Tapping hole  $\varnothing$ : 95.11 mm

**Technical description**

Thread depth	152.4 mm
Shank square $\square$	44 mm
Shank $\varnothing D_s$	56 mm
Number of cutting edges Z	12
Thread pitch	6.35 mm
Tapping hole $\varnothing$	95.11 mm
Thread $\varnothing$	101.6 mm

Overall length L	180 mm
Number of clamping slots	12
Threads per inch	4
Tool material	HSS
Thread type	UNC-LH
Thread size	4-4 UNC LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap