

**Garant**
**Left-hand thread through hole and blind hole machine tap, TiN, Type: 2.1/2-14**

**Order data**

Order number	130056 2.1/2-14
GTIN	4062406055776
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS

Threads per inch: 14

Thread  $\varnothing$ : 63.5 mm

Overall length L: 160 mm

Shank  $\varnothing$  D<sub>s</sub>: 50 mm

Shank square  $\square$ : 39 mm

Tapping hole  $\varnothing$ : 61.75 mm

**Technical description**

Shank $\varnothing$ D <sub>s</sub>	50 mm
Overall length L	160 mm
Tapping hole $\varnothing$	61.75 mm
Tool material	HSS
Number of cutting edges Z	6
Number of clamping slots	6
Thread $\varnothing$	63.5 mm

Thread pitch	1.814 mm
Thread depth	95.25 mm
Threads per inch	14
Shank square □	39 mm
Thread type	UNS-LH
Thread size	2.1/2-14 UNS LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap