

HOLEX®
**Side lock arbor Form ADB with cooling channels, SK 50 short, Clamping range
 Ø D1: 18 mm**

Order data

Order number	300305 18
GTIN	4045197701305
Item class	32A

Description
Version:

With Balluffchip bore.

With cooling channels.
Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Overhang dimension A: 63 mm

External Ø D: 50 mm

Spare clamping screw 309900: 16

Technical description

Spare clamping screw 309900	16
Clamping Ø D ₁	18 mm
Overhang dimension A	63 mm
External Ø D	50 mm
Adapter	SK 50 short
Norm	DIN 6359

Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC

Accessories

Torque insert for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308810 50
Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308820 50
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50	308605 50
Pull stud stud sealed, form A suitable for steep tapers 50	308610 50
Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 50 SK	308830 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50
Torque insert for Pull studs to SO 7388 suitable for steep tapers 50 SK	308812 50
Pull stud sealed suitable for steep tapers 50	308660 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Pull stud 45° sealed suitable for steep tapers 50	308765 50
Special pull stud with no internal thread sealed suitable for steep tapers 50	308700 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
Pull stud Form B suitable for steep tapers 50	308640 50

Pull stud 45° sealed suitable for steep tapers 50	308760 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50	308615 50
Pull stud Form A suitable for steep tapers 50	308600 50
Pull stud sealed, form B suitable for steep tapers 50	308620 50
Pull stud sealed, form B suitable for steep tapers 50	308650 50