

**Garant****Holder for Weldon shanks, cylindrical, slim, Clamping range Ø D1: 18mm****Order data**

Order number	300415 18
GTIN	4045197701848
Item class	31A

**Description****Version:**

Cylindrical holder with Weldon shank and a clamping screw for clamping the tool. Ø6 mm through hole for **internal cooling** provided.

**Version:**

Type of clamping screw: M14 × 1 – SKT 5

**Advantage:**

Low interference contour due to slim design and variation of the clamped lengths.

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Supplied with:**

Including insert screw No. 300416.

**Technical description**

Overall length L	156 mm
Ø D <sub>2</sub>	28 mm
Clamping Ø D <sub>1</sub>	18 mm
L <sub>1</sub>	100 mm
External Ø D	25 mm
Through-coolant	yes
Type of product	Side lock arbor

## Accessories

Pull studsealed, form B suitable for steep tapers 40	308650 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studsealed, form A suitable for steep tapers 30	308610 30
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studsealed, form A suitable for steep tapers 50	308610 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 45°sealed suitable for steep tapers 30	308760 30
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull studForm A suitable for steep tapers 50	308600 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 60°sealed suitable for steep tapers 30	308785 30
Pull studForm B suitable for steep tapers 50	308640 50

Pull studsealed suitable for steep tapers 40	308660 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed suitable for steep tapers 50	308660 50
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studForm A suitable for steep tapers 40	308600 40
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Clamping screw for micro-clamp arbor Thread size M14	300416 M14
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud 45°sealed suitable for steep tapers 30	308765 30
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40