

Garant
Spiral flute machine tap, uncoated, MF: M43X1

Order data

Order number	130010 M43X1
GTIN	4062406057237
Item class	10N

Description
Note:

Minimum order quantity: 1 pc.

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 1 mm

Overall length L: 220 mm

Shank \varnothing D_s: 36 mm

Shank square \square : 29 mm

Tapping hole \varnothing : 42 mm

Technical description

Number of cutting edges Z	4
Overall length L	220 mm
Standard	DIN 376
Tapping hole \varnothing	42 mm
Thread \varnothing	43 mm
Thread pitch	1 mm
Shank square \square	29 mm

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	36 mm
Thread type	M
Tool material	HSS E
Number of clamping slots	4
Thread depth	107.5 mm
Thread size	M43×1
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without

Type of product

Tap