

Garant**WNMG 060408, Grade: HB7210-1**

Order data

Order number	252064 HB7210-1
GTIN	4062406059132
Item class	21G

Description

WNMG 060408 HB7210-1 Grade: HB7210-1

Chip breaker: GM

Tolerance: M

Cutting depth a_p : 0.4 - 6.5 mmFeed f : 0.3 - 0.7 mm/rev.Cutting speed v_c main application: 100 - 450 m/min

Technical description

Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Feed f	0.3 - 0.7 mm/rev.
Cutting speed v_c main application	100 - 450 m/min
Chip breaker	GM
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Cutting depth a_p	0.4 - 6.5 mm

Tool material	Carbide
Main application	K
Grade	HB7210-1
Coating	TiCN
ISO code indexable insert	WNMG 060408
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning