



## High feed rate milling cutter MFH mini, with thread, $\varnothing D$ / number of teeth Z: 40/5mm



### Order data

Order number	221960 40/5
GTIN	2050002058743
Item class	250

### Technical description

Mounting thread M	M16
Circular interpolation milling $\varnothing D_{\min}$	73 mm
Cutting edge $\varnothing D_c$	40 mm
Overall length $L_{\text{tot}}$	40 mm
Ramping angle $\alpha_{\max}$	0.55 degrees
Number of cutting edges Z	5
$\varnothing D_3$	33 mm
maximum cutting depth $a_{p\max}$	1 mm
Circular interpolation milling $\varnothing D_{\max}$	78 mm
Ramping length L for $\alpha_{\max}$	31.3 mm
Insert screw	229713 (8IP; 1.2 Nm)
suitable indexable insert	LOGU 0303..
Through-coolant	yes

Shank type	with thread
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

---

## Accessories

Clamping screw	229713
----------------	--------