

Garant
Circular mill, with thread steel, Type: 16/M5

Order data

Order number	217253 16/M5
GTIN	4062406060060
Item class	21Q

Description
Version:
Extra-slim version for thread milling.

Note:

The actual groove depth S_{max} is calculated as follows: $(D-d_1) / 2$.

Tool exchange: PowerCard

Through-coolant: yes

smallest hole $\varnothing D$: 14 - 22 mm

Thread size M: M5 mm

for insert type: P16

Internal $\varnothing d_1$: 9.5 mm

maximum cutting depth S_{max} : 6.5 mm

Overhang L_1 : 15 mm

Technical description

Thread depth	15 mm
Overhang L_1	15 mm
maximum cutting depth S_{max}	6.5 mm
Internal $\varnothing d_1$	9.5 mm
Thread size M	M5 mm

Shank type	with thread
Overall length L_{tot}	18.5 mm
Through-coolant	yes
for insert type	P16
smallest hole $\varnothing D$	14 - 22 mm
Set of insert screws	219818 (8IP; 3.8 Nm)
Material of milling tool	with thread steel
Tool exchange	PowerCard
Type of product	Circular mills