


TNMG 160404, Grade: PR005S

Order data

Order number	251472 PR005S
GTIN	4960664836697
Item class	25E

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.03 - 0.25 mm/rev.
Cutting conditions	continuous
Corner radius	0.4 mm
Grade	PR005S
Tool material	Carbide
Finishing/roughing assignment	Finishing
Chip breaker	MQ
Main application	S
Cutting speed v_c main application	30 - 90 m/min
Coating	Megacoat Hard
ISO code indexable insert	TNMG 160404
Number of changes/inserts	6

Type of product

Indexable insert for turning