

Garant

**Indexable face mill 45° right-hand cutting, with bore, Ø D / number of teeth Z:
125/7mm**

**Order data**

Order number	214200 125/7
GTIN	4045197702357
Item class	210

Description**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 5.7** with bit shank No. **674252 size 20IP**.

Technical description

suitable indexable insert	SE.. 1204..
Overall length L_{tot}	63 mm
Mounting bore \varnothing	40 mm
Cutting edge $\varnothing D_c$	125 mm
Pack of insert screws	219800 (20IP; 5.7 Nm)
maximum external $\varnothing D_{max}$	138 mm
Number of cutting edges Z	7
Shank type	with bore

Setting angle κ	45 degrees
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	Face mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP
Set of insert screws 10 pieces	219800
Torque screwdriver, fixed setting set torque 5,7 N·m	211750 5,7