

Garant**Workshop vernier caliper with fine adjustment, Measuring range: 300mm****Order data**

| | |
|--------------|---------------|
| Order number | 415090 300 |
| GTIN | 4062406065102 |
| Item class | 40Z |

Description**Version:**

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale for ease of reading both internal and external measured values. Direct reading of internal dimensions by additional scale. With fine adjustment. With locking screw. Size 300 through hardened, from size 500 measuring faces hardened.

Technical description

| | |
|-----------------------------|---------------|
| Packaging | sturdy box |
| Measuring range | 0 - 300 mm |
| Internal jaw \varnothing | 10 mm |
| Jaw length | 90 mm |
| Calibration | A1 |
| Graduation | 1/20 mm |
| Standard | ISO 13385 |
| Measurement deviation E MPE | ± 0.05 mm |
| Fine setting | yes |
| Measuring tips | yes |
| Measurement technology | analogue |

| | |
|-----------------|-----------------------|
| Material | Stainless steel, INOX |
| Type of product | Workshop calipers |

Services

| | |
|--|------------|
| DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm | 021010 300 |
| Calibration Calipers / depth gauges maximum measuring range 300 mm | 021000 300 |