

Garant**Workshop vernier caliper with fine adjustment, Measuring range: 500mm****Order data**

Order number	415090 500
GTIN	4062406065218
Item class	40Z

Description**Version:**

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale for ease of reading both internal and external measured values. Direct reading of internal dimensions by additional scale. With fine adjustment. With locking screw. Size 300 through hardened, from size 500 measuring faces hardened.

Technical description

Jaw length	150 mm
Packaging	sturdy box
Calibration	A1
Graduation	1/20 mm
Internal jaw \varnothing	20 mm
Measuring range	0 - 500 mm
Standard	ISO 13385
Measurement deviation E MPE	± 0.07 mm
Fine setting	yes
Measuring tips	yes
Measurement technology	analogue

Material	Stainless steel, INOX
Type of product	Workshop calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500
CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500