

Garant**Workshop vernier caliper with fine adjustment, Measuring range: 750mm****Order data**

Order number	415090 750
GTIN	4062406065225
Item class	40Z

Description**Version:**

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale for ease of reading both internal and external measured values. Direct reading of internal dimensions by additional scale. With fine adjustment. With locking screw. Size 300 through hardened, from size 500 measuring faces hardened.

Technical description

Measuring range	0 - 750 mm
Internal jaw \varnothing	20 mm
Graduation	1/20 mm
Calibration	A1
Packaging	sturdy box
Standard	ISO 13385
Jaw length	150 mm
Measurement deviation E MPE	± 0.10 mm
Fine setting	yes
Measuring tips	yes
Measurement technology	analogue

Material	Stainless steel, INOX
Type of product	Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000