

Garant**Face mill arbor tapered, SK 50 A = 400, Spigot Ø d1: 16mm****Order data**

Order number	301145 16
GTIN	4045197702777
Item class	31A

Description**Version:**

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- With RFID / Balluffchip bore.
- Larger collar contact face.

Vibration damped version, arbor with vibration-damping core.

Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Note:

Further sizes on request.

Technical description

Milling mandrel length L_4	17 mm
Overhang dimension A	400 mm
Spigot Ø d ₁	16 mm
External Ø D	80 mm
Ø D ₂	38 mm
L ₂	355 mm

Weight	10.5 kg
Clamping Ø D ₁	16 mm
Adapter	SK 50 A = 400
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/301145-16>