

**Garant**

**Face mill arbor with cooling channel bores, PSC 63 A = 65, Spigot  $\varnothing$  d1: 22mm**


**Order data**

Order number	308547 22
GTIN	4045197703729
Item class	31C

**Description**
**Version:**

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

**Application:**

For holding shell end mills and face mills with cross keyway.

**Supplied with:**

Lock screw.

**Optional extras:**

Toggle spanner No. 309840, cutter lock screw No. 309860.

Coolant tube and assembling key for coolant tubes No. 309885; 309893.

**Technical description**

Suitable toggle spanner No. 309840	22
Spigot $\varnothing$ d <sub>1</sub>	22 mm
Spare milling cutter lock screw No. 309860 / 309861	22
Overhang dimension A	65 mm
External $\varnothing$ D	48 mm
Clamping $\varnothing$ D <sub>1</sub>	22 mm

Adapter	PSC 63 A = 65
Arbor standard	ISO 26623-1
Cooling channel bore	pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Type of product	Milling head arbor

---

## Accessories

Toggle spanner for mandrel Ø 22 mm	309840 22
------------------------------------	-----------