

Garant GRIDLINE

**Base cabinet with drawer, Plain sheet metal swing doors, 16×16G, Height: 800mm****Order data**

Order number	940021 800
GTIN	4062406067182
Item class	9GI

**Description****Version:**

Equipped cabinet in 20×20G, with drawers 16×16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door. Drawers with front height 125 mm.

**Supplied with:**

Cabinet with shelves and drawers.

**Colour:**

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Usable height	645 mm
Width	500 mm
Drawer runner extension (partial/full extension)	100 %
Drawer/pull-out shelf load capacity	75 kg
Cabinet fronts	Plain sheet metal swing door
Number of drawers	1
Electronic locking system can be retrofitted	yes
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
ComfortClose	no
Handle positioning	top
Weight	35 kg
Number of shelves	1
Height	800 mm
Depth	500 mm
Drawer usable width	400 mm
Drawer usable width in G	16
Depth in G	20
Drawer usable depth in G	16
Drawer usable depth	400 mm
Width in G	20
Drawer usable area in G	16×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable width × usable depth in G	16×16G
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm	940640 75
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets,Width 20G Drawer front height 100 mm	940640 100
Ribbed rubber mat for drawers Dimension in G 16X16	951910 16X16
Storage shelf for cabinet / compartment width in G 20	940550 20
Non-slip mats set for drawers,5 pieces Dimension in G 16X16	951885 16X16
Cover made of laminated wood Dimension in G 20X20	951985 20X20
Cover made of bamboo Dimension in G 20X20	951980 20X20
Storage shelf slotted for cabinet / compartment width in G 20	940552 20
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Inclined shelf for cabinet / compartment width in G 20	940560 20
Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm	940501 750/800
Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm	940640 125