

Garant GRIDLINE

**Top-mounted cabinet with drawer, Plain sheet metal swing doors, 26×16G,
Height: 750mm****Order data**

| | |
|--------------|---------------|
| Order number | 940071 750 |
| GTIN | 4062406067670 |
| Item class | 9GI |

Description**Version:**

Equipped cabinet in 30×20G, with drawers 26×16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door. drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|---|--|
| Number of shelves | 1 |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg |
| Drawer/pull-out shelf load capacity | 75 kg |
| Handle positioning | bottom |
| Weight | 43 kg |
| Usable height | 595 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Number of drawers | 1 |
| Cabinet fronts | Plain sheet metal swing door |
| ComfortClose | no |
| Width | 750 mm |
| Depth | 500 mm |
| Height | 750 mm |
| Electronic locking system can be retrofitted | yes |
| Drawer usable depth | 400 mm |
| Width in G | 30 |
| Drawer usable depth in G | 16 |
| Depth in G | 20 |
| Drawer usable width in G | 26 |
| Drawer usable width | 650 mm |
| Drawer usable area in G | 26×16 |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1000 kg |
| Door opening angle | 250 degrees |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |

| | |
|---|----------------------|
| Drawer usable width × usable depth in G | 26×16G |
| Type of cabinet | Add-on cabinet |
| Type of product | Cabinet with shelves |

Accessories

| | |
|--|----------------|
| Drawer for swing-door cabinets,Width 30G Drawer front height 150 mm | 940641 150 |
| Drawer for swing-door cabinets,Width 30G Drawer front height 100 mm | 940641 100 |
| Slide handle for GridLine Type GP11 | 914226 GP11 |
| Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm | 940501 750/800 |
| Non-slip mats set for drawers,5 pieces Dimension in G 26X16 | 951885 26X16 |
| Extended lighting set for GridLine cabinets withSwing doors, width 30G for cabinet height 750/800 mm | 940510 750/800 |
| Comfort Close drawer closure damping system Load capacity of the drawer 75 kg | 950180 75 |
| Ribbed rubber mat for drawers Dimension in G 26X16 | 951910 26X16 |
| Drawer for swing-door cabinets,Width 30G Drawer front height 125 mm | 940641 125 |
| Mat for drawers Dimension in G 26X16 | 951830 26X16 |
| Storage shelf slotted for cabinet / compartment width in G 30 | 940552 30 |
| Storage shelf for cabinet / compartment width in G 30 | 940550 30 |
| Drawer for swing-door cabinets,Width 30G Drawer front height 300 mm | 940641 300 |
| Inclined shelf for cabinet / compartment width in G 30 | 940560 30 |
| Shelf clip set for GridLine cabinets20 pieces Type F | 940559 F |
| Drawer for swing-door cabinets,Width 30G Drawer front height 200 mm | 940641 200 |

Storage shelf 200 kg for cabinet / compartment width in G
30

940590 30

Drawer for swing-door cabinets, Width 30G Drawer front
height 75 mm

940641 75