


Garant GRIDLINE

## Drawer for swing-door cabinets, Width 40G, 36×16G, Drawer front height: 200mm



### Order data

Order number	940642 200
GTIN	4062406068363
Item class	9GI

### Description

#### Version:

Drawers for installation in GridLine cabinets. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with dividing material.

#### Suitable for:

Cabinets No. 940001 – 940103; No. 940111 – 940113, No. 940801 – 940843.

#### Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

Unsuitable for installation in sliding door cabinets.

### Technical description

Usable width in G	36
Usable depth in G	16
Drawer/pull-out shelf load capacity	75 kg
Weight	19 kg
Usable height	175 mm
Application range	Cabinet with shelves
Usable width	900 mm
Usable depth	400 mm

with individual drawer release system	no
Material thickness	0.9 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×16G
Type of product	Drawer

## Accessories

Mat for drawers Dimension in G 36X16	951830 36X16
Ribbed rubber mat for drawers Dimension in G 36X16	951910 36X16
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Non-slip mats set for drawers,5 pieces Dimension in G 36X16	951885 36X16