

Garant GRIDLINE

**Base cabinet with Viewing window sliding doors, Height: 1500mm****Order data**

Order number	940127 1500
GTIN	4062406069094
Item class	9GI

**Description****Version:**

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Height	1500 mm
--------	---------

Depth in G	20
Depth	500 mm
Number of shelves	3
ComfortClose	no
Width in G	50
Weight	120 kg
Handle positioning	top
Usable height	1345 mm
Width	1250 mm
Cabinet fronts	Viewing window sliding door
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Electronic locking system can be retrofitted	yes
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Inclined shelf for cabinet / compartment width in G 50	940560 50
Storage shelf slotted for cabinet / compartment width in G 50	940552 50
Cover made of bamboo Dimension in G 50X20	951980 50X20
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
	940513 1500

Extended lighting set for GridLine cabinets with Sliding doors, width 50G for cabinet height 1500 mm

Storage shelf 200 kg for cabinet / compartment width in G 50

940590 50

Cover made of laminated wood Dimension in G 50X20

951985 50X20

Storage shelf for cabinet / compartment width in G 50

940550 50

Base with removable fascia, depth 20G, Height 150 mm  
Cabinet casing in G 50

958146 50

Lock plate for GridLine Type GP21

914227 GP21