

**Mobile workbench 179NW, Type: 179NW-7****Order data**

Order number	918279 179NW-7
GTIN	4000896219629
Item class	93H

Description**Version:**

Mobile workbench with 7 drawers and cupboard section with an adjustable shelf. Central locking with cylinder lock and anti-tilt device on both sides. Cabinet with edge protection corners throughout. Drawer load capacity 25 kg, one heavy-duty drawer rated at 40 kg load capacity. Worktop made of Birch marine ply, suitable for flexible mounting of vice, exchangeable. Overall load capacity 750 kg. 2 castors with parking brake, and 2 fixed wheels.

Fitted with:

Number×drawer front height mm: 6×81 / 1×166

Colour:

Blue

Technical description

Drawer usable width	522 mm
Weight	120 kg
Height	964 mm
Drawer usable depth	398 mm
Series	Assistent

Worktop thickness	30 mm
Depth	600 mm
Width	1150 mm
Type	179NW-7
Configurator relevant	no
Drawer/pull-out shelf load capacity	25 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Type of product	mobile workbench